



**Inch table**

Dimensions in: inches - millimeters

Length <b>l</b>	<b>d</b> <sub>1</sub> +0.001 Bore	<b>s</b> +0.002 Square	<b>d</b> <sub>2</sub>	<b>d</b> <sub>3</sub>	<b>h</b> <sub>1</sub>	<b>h</b> <sub>2</sub>	<b>h</b> <sub>3</sub>	<b>h</b> <sub>4</sub>	<b>h</b> <sub>5</sub> ≈	Ø Handle GN 598	
3.94 100	B 1/2	-	V 1/2	1.06 27	1.18 30	1.10 28	0.67 17	0.51 13	0.77 19.5	2.66 67.5	0.91 23
4.92 125	B 5/8	-	V 5/8	1.26 32	1.38 35	1.34 34	0.87 22	0.55 14	0.77 19.5	2.66 67.5	0.91 23
6.30 160	B 1/2	B 3/4	V 3/4	1.38 35	1.54 39	1.50 38	1.02 26	0.63 16	0.77 19.5	3.25 82.5	1.02 26

**Metric table**

Dimensions in: millimeters - inches

Length <b>l</b>	<b>d</b> <sub>1</sub> H7 Bore	<b>s</b> H11 Square	<b>d</b> <sub>2</sub>	<b>d</b> <sub>3</sub>	<b>h</b> <sub>1</sub>	<b>h</b> <sub>2</sub>	<b>h</b> <sub>3</sub>	<b>h</b> <sub>4</sub>	<b>h</b> <sub>5</sub> ≈	Ø Handle GN 598
100 3.94	B 12	V 12	27 1.06	30 1.18	28 1.10	17 0.67	13 0.51	19.5 0.77	67.5 2.66	23 0.91
125 4.92	B 14	V 14	32 1.26	35 1.38	34 1.34	22 0.87	14 0.55	19.5 0.77	67.5 2.66	23 0.91
160 6.30	B 17	V 17	35 1.38	39 1.54	38 1.50	26 1.02	16 0.63	19.5 0.77	82.5 3.25	26 1.02

**Specification**

- Crank body  
Aluminum  
- Powder coated  
Black, textured finish  
- Contact face of hub machined
- Retractable handle GN 598.3 → page 50  
Plastic  
Duroplast (Phenolic PF)  
- Black, shiny finish  
- Retractable mechanism  
Steel, blackened finish
- Square Bores DIN 79 → page 2044
- Cross Holes GN 110 → page 2042
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

GN 471.3 crank handles are mainly used for applications where the hand piece must not protrude. In the operating position, the hand piece is firmly locked. By pulling the hand piece in the axial direction out of its locating cone, it can be folded back into place. The spring holds the hand piece firmly in both positions.

see also...

- Crank Handles EN 570.3 (Technopolymer Plastic, with Blind Bore) → www.jwwinco.com

**On request**

- Other modifications such as special inch and metric bores, squares, keyways, set screw holes, etc.
- With EN 598.5 retractable handles (Stainless steel retractable mechanism)

How to order	<b>1</b> Length <b>l</b>
	<b>2</b> Square <b>s</b> (Bore <b>d</b> <sub>1</sub> )

**GN 471.3-125-V14**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4