



Metric table



Dimensions in: millimeters - inches

Length l	a	b	d Thread	h	t min.
86 ±0.5 3.39 ±0.02	17 0.67	26 1.02	M 6	43 1.69	12 0.47
117 ±0.5 4.61 ±0.02	20 0.79	30 1.18	M 8	54 2.13	13 0.51
179 ±1.0 7.05 ±0.04	20 0.79	30 1.18	M 8	62 2.44	13 0.51

Specification

- Body
Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, shiny finish
 - Flash mark cleaned and polished
- Tapped inserts
Brass
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

EN 525 cabinet "U" handles have an ergonomic design and aesthetically appealing shiny finish.

see also...

- Cabinet "U" Handles GN 565 (Aluminum) → page 98

How to order

EN 525-117

1 Length l