



- 2 Type**
- A** With arrow
  - B** Neutral
  - S** With scale 0...9, 40 and/or 100 graduations

**Metric table**

Dimensions in: millimeters - inches

<b>d<sub>0</sub></b> Knurled control knob Ø EN 526	<b>d<sub>1</sub></b>	<b>l<sub>1</sub></b>	<b>l<sub>2</sub></b>	<b>s</b>	Number of graduation marks Type S
32 1.26	38 1.50	6 0.24	32 1.26	0.8 0.03	40 1.57
42 1.65	50 1.97	7 0.28	39 1.54	1 0.04	40 1.57
48 1.89	55 2.17	8 0.31	43 1.69	1 0.04	100 3.94
52 2.05	63 2.48	9 0.35	48 1.89	1 0.04	100 3.94
63 2.48	78 3.07	13 0.51	57 2.24	1 0.04	100 3.94

**Specification**

- Aluminum  
Anodized finish, natural color
- Arrow (Type A) and scale (Type S)  
Black, printed
- RoHS compliant

**On request**

- Special graduations, laser-engraved  
see "How to order Graduations" → page QVX

**Information**

EN 526.1 control knob flanges are specifically designed to fit EN 526 knurled control knobs. Also, these control knob flanges can be supplied with any type of graduation.

Regarding design, numbering position and numbering sequence of the scale please see the layout for scale knobs on the order form "How to order Graduations".

see also...

- Knurled Control Knobs GN 726.2 (Aluminum) → page QVX
- Knurled Control Knobs GN 723.4 (Aluminum) → page QVX

<p>How to order</p> <p><b>EN 526.1-50-A</b></p>	<b>1</b> Outside diameter d <sub>1</sub>
	<b>2</b> Type