



**SS** Stainless Steel

**Type**

- C** Open eye
- E\*** Closed eye

**Metric table**



Dimensions in: millimeters - inches

Length l	Type E	b	d1	d2	d3	f	m	Static load ≈
Type C	Type E	Type E	Type C	min.		min.	min.	
40 1.57	-	-	6 0.24	11 0.43	4 0.16	4.5 0.18	5 0.20	500 N 112 lbf
50 1.97	50 1.97	5.3 0.21	8 0.31	15 0.59	5 0.20	5.5 0.22	7 0.28	1200 N 270 lbf
60 2.36	60 2.36	6.4 0.25	9 0.35	17 0.67	6 0.24	6.5 0.26	8 0.31	1200 N 270 lbf

\* Only available in stainless steel

**Specification**



- Steel **ST**
- Zinc plated **ZB**
- Stainless steel **A4**
- Plain finish **BL**
- *Stainless Steel Characteristics* → page QVX
- **RoHS**

**Accessory**

- Key Rings GN 111.3 → page QVX

**Information**

Carabiners GN 5299 are used, for example, to connect tools or other components quickly and without tools or to secure them against loss. The carabiner is opened by hand and closes automatically by a concealed spring when released.

The eye of type E, which is fitted with a pressed-in, closed round thimble, enables captive mounting of the carabiners, e.g. by means of an appropriately pressed retaining cable.

Carabiners GN 5299 must not be used for lifting loads or lashing. The data on load capacity are approximate values to the exclusion of any liability.

see also...

- *Retaining Cables GN 111.2 (Stainless Steel)* → page QVX
- *Retaining Cables GN 111.8 (Stainless Steel AISI 316)* → page QVX
- *Ball Chains GN 111 (Brass)* → page QVX
- *Ball Chains GN 111.5 (Stainless Steel)* → page QVX
- *Spiral Retaining Cables GN 111.4 (Plastic)* → page QVX

How to order	1	Type
 <b>GN 5299-C-50-ST-ZB</b>	2	Length l
	3	Material
	4	Finish