



Metric table

Dimensions in: millimeters - inches

n	d	1						2						b	h ₁	h ₂	l ₂
		3						3									
		Steel						Stainless Steel									
8 0.31	M 6	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	16 0.63	4.5 0.18	1.5 0.6	8 0.32	
8 0.31	M 8	20 0.79	25 0.98	30 1.18	-	-	-	-	-	-	-	-	16 0.63	4.5 0.18	1.5 0.6	8 0.32	
10 0.39	M 6	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	19.5 0.78	5.5 0.22	4 0.16	8.5 0.33	
10 0.39	M 8	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	-	20 0.79	25 0.98	30 1.18	40 1.57	60 2.36	19.5 0.78	5.5 0.22	4 0.16	8.5 0.33	

Specification

- Steel, zinc plated, blue passivated finish **SZ**
- Stainless steel, plain finish **NB**
- RoHS

Accessory

- Collar nuts GN 53b → page XYZ

Information

T-slot bolts GN 52b fasten attachments and accessories in the slot of aluminum profiles. They are inserted into the slot of the aluminum profile at any position and affixed by a 90° turn.

The connection is conductive.

see also...

- Aluminum Profiles GN 10b (Profile Type Light) → page QVX
- Aluminum Profiles GN 10b (Profile Type Heavy) → page QVX

How to order	1 Slot width n
	2 Thread d
	3 Length l ₁
	4 Material / Finish

1 2 3 4
GN 52b-10M830-SZ