



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	<sup>3</sup> Length l	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>
45 1.77	M 6	20 0.79	19 0.75	25 0.98	22.5 0.89
45 1.77	M 8	25 0.98	19 0.75	25 0.98	22.5 0.89
63 2.48	M 8	25 0.98	26 1.02	28 1.10	25 0.98
80 3.15	M 10	30 1.18	32 1.26	36 1.42	30 1.18
100 3.94	M 12	40 1.57	36 1.42	42 1.65	36 1.42

**Specification**

- Three-lobed knob  
Plastic  
Technopolymer (Polyamide PA)
  - Glass fiber reinforced
  - Temperature resistant up to 266 °F (130 °C)
  - Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- [RoHS compliant](#)

**Information**

EN 5330 three-lobed knobs have been developed for heavy duty applications. Due to its shape, higher torque can be achieved.

<p>How to order</p> <p><b>EN 5330-100-M12-40</b></p>	<sup>1</sup> <sup>2</sup> <sup>3</sup>	1 Handle diameter d <sub>1</sub>
		2 Thread d <sub>2</sub>
		3 Length l