



SS Stainless Steel

Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂ GN 5334	³ Length l				d ₄	h ₁ ≈	h ₂ ≈
1.57 40	5/16 x 18	0.79 20	0.98 25	1.57 40	0.55 14	0.94 24	0.47 12	
1.97 50	3/8 x 16	0.79 20	0.98 25	1.57 40	0.71 18	1.18 30	0.65 16.5	
2.36 60	1/2 x 13	0.98 25	1.57 40	1.97 50	0.79 20	1.48 37.5	0.79 20	

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ GN 5334 / GN 5334.4	³ Length l				d ₄	h ₁ ≈	h ₂ ≈	
32 1.26	M 6	16 0.63	20 0.79	30 1.18	-	12 0.47	21 0.83	10 0.39	
40 1.57	M 8	20 0.79	30 1.18	40 1.57	50 1.97	14 0.55	24 0.94	12 0.47	
50 1.97	M 10	20 0.79	30 1.18	40 1.57	50 1.97	60 2.36	18 0.71	30 1.18	16.5 0.65
60 2.36	M 12	20 0.79	30 1.18	40 1.57	50 1.97	60 2.36	20 0.79	37.5 1.48	20 0.79

Specification

- **GN 5334**
Stainless steel AISI 304
- **GN 5334.4**
Stainless steel AISI 316L

This information applies to both series:

- Knob drawn from stainless steel sheet
- Hub with threaded stud welded
- Matte shot-blasted finish

• [Stainless Steel Characteristics](#) → page 2143

• [RoHS compliant](#)

On request

- Other stud lengths

Information

The original ELESA design with 5 recess grips is typical for star knobs GN 5334 / GN 5334.4.

This form gives these grips an appealing look and additionally allows a high torque to be achieved.

Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

- [Wing Screws GN 835 \(Stainless Steel\)](#) → page 677
- [Star Knobs GN 6336.5 \(Stainless Steel\)](#) → page 578
- [Hand Knobs GN 6335.5 \(Stainless Steel\)](#) → page 632
- [Star Knobs GN 5334.4 with Loss Protection GN 111.7 \(Stainless Steel\)](#) → page 2046

How to order (Inch, stainless steel AISI 304)	¹ Handle diameter d ₁
GN 5334-50-3/8X16-40	² Thread d ₂
	³ Length l

How to order (Metric, stainless steel AISI 316L)	¹ Handle diameter d ₁
GN 5334.4-60-M12-30	² Thread d ₂
	³ Length l