



Metric table

Dimensions in: millimeters - inches

¹ n	² d ₁	d ₂ ≈	h	s
8 0.31	M 6	14 0.55	6 0.24	10 0.39
10 0.39	M 8	21 0.83	8 0.31	13 0.51

Specification

- Steel, zinc plated, blue passivated finish **SZ**
- RoHS

Accessory

- T-slot bolts GN 52b → page QVX

Information

Collar nuts GN 53b fasten attachments and accessories in the slot of aluminum profiles, generally in combination with T-slot bolts GN 52b.

The collar makes a washer unnecessary.

see also...

- Aluminum Profiles GN 10b (Profile Type Light) → page QVX
- Aluminum Profiles GN 10b (Profile Type Heavy) → page QVX

How to order

¹ ² ³
GN 53b-10M8-SZ

1 Slot width n

2 Thread d₁

3 Material / Finish