



Metric table



Dimensions in: millimeters - inches

| d ₁ Pipe thread | Fine thread | d ₂ | Length l | t |
|-------------------------------|-------------|----------------|------------|------------|
| G 1 | - | 42 1.65 | 16 0.63 | 11 0.43 |
| G 2 | M 60 x 2 | 70 2.76 | 26 1.02 | 18 0.71 |

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal
Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

EN 548.2 fluid retention caps can be used as permanent caps or temporary caps to protect the tank from foreign objects entering the vessel.

| | |
|--------------------|--|
| How to order | 1 Pipe thread d ₁ (Fine thread d ₁) |
| EN 548.2-G1 | |

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

