



- 2 Type**
- A** Closed type
 - B** Open-end type, mounting from the back (tapped blind hole)
 - C** Open-end type, mounting from the operator's side

Metric table

1 Dimensions in: millimeters - inches

$l_1 \pm 0.25$	a_1	a_2	a_3	b_1	b_2	d_1	d_2	h_1	h_2	h_3	h_4	h_5	l_2	$l_3 \pm 0.2$	l_4	l_5	l_6	l_7	t_1 min.	t_2 min.	t_3
162	38	19	40	25	28	M 8	8.3	55	57	36	38	28	128	140	8	22	10	20	12	16	8
6.38	1.50	0.75	1.57	0.98	1.10		0.33	2.17	2.24	1.42	1.50	1.10	5.04	5.51	0.31	0.87	0.39	0.79	0.47	0.63	0.31

Specification

- Body
Aluminum
- Powder coated
Black, RAL 9005, textured finish **● SW**
Silver, RAL 9006, textured finish **● SR**
- Cover cap (Type C)
Plastic
- Black (for SW)
- Light gray (for SR)
- Load Rating Information → page 2068
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

GN 559 open-end or closed-end type cabinet / door handles are mainly used in applications requiring a sturdy and rugged grip.

A special characteristic of the GN 559 is the thumb rest pad on the front leg.

Because of the dual mounting holes, there is a choice of two center hole mountings on the closed-end handle. Due to the dual mounting holes on the open-end handle, the handle is secured tightly into position after installation.

How to order	1 Length l_1
GN 559-162-B-SW	2 Type
	3 Finish