



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side (only for $b_1 = 26$ mm)

Metric table

Dimensions in: millimeters - inches

1 b_1	2 Length $l \pm 0.25$	a	b₂	b₃	b₄	b₅ +1	d₁ Type A	d₂ Type B	h₁	h₂	r	t min.
20 0.79	112 4.41	13 0.51	24 0.94	32 1.26	50 1.97	13.5 0.53	M 6	-	32 1.26	48 1.89	13 0.51	10 0.39
20 0.79	128 5.04	13 0.51	24 0.94	32 1.26	50 1.97	13.5 0.53	M 6	-	32 1.26	48 1.89	13 0.51	10 0.39
26 1.02	128 5.04	17 0.67	32 1.26	34 1.34	57 2.24	18 0.71	M 8	M 6	34 1.34	54 2.13	17 0.67	12 0.47
26 1.02	160 6.30	17 0.67	32 1.26	34 1.34	57 2.24	18 0.71	M 8	M 6	34 1.34	54 2.13	17 0.67	12 0.47

Specification

- Body
 - Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Silver, RAL 9006, textured finish **● SR**
 - Anodized finish, natural color **● EL**
 - Plain, tumbled finish **● BL**
- Type B
 - Socket button head screws ISO 7380-M6-25
 - Hex nuts ISO 4032-M6
 - Washers DIN 125
 - Steel, zinc plated, blue passivated finish
- Load Rating Information → page 2068
- RoHS compliant

Information

GN 565.2 angled cabinet “U” handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

The 35° angled contact surface allows improved access even in tight spaces such as corners.

For type B, socket button head screws, hex and washers are included.

see also...

- Product Family Standard Parts for Profile Systems → page 18
- Cabinet “U” Handles GN 425.1 (Offset) → page 144 / 145
- Cabinet “U” Handles GN 426.1 (Aluminum, Offset) → page 150
- Off-Set Open “U” Handles EN 630.1 (Plastic) → page 108
- T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems) → page 2048
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems) → page 2058

How to order	1 Handle width b_1
1 2 3 4	2 Length l
	3 Type
	4 Finish

GN 565.2-26-128-B-SW