



SS Stainless Steel

**3 Type**

- A Mounting from the back (tapped blind hole)
- B Mounting from the operator's side

**Metric table**

Dimensions in: millimeters - inches

b		l <sub>1</sub>	a	d <sub>1</sub>	d <sub>2</sub>	h <sub>1</sub> ≈	h <sub>2</sub>	l <sub>2</sub> ≈	t <sub>1</sub> min.	t <sub>2</sub>
GN 565.4	GN 565.9			Type A	Type B					
20 0.79	20 0.79	160 6.30	13 0.51	M 6	5.3 0.21	50 1.97	5 0.20	185 7.28	8 0.31	5 0.20
20 0.79	20 0.79	192 7.56	13 0.51	M 6	5.3 0.21	50 1.97	5 0.20	221 8.70	8 0.31	5 0.20
26 1.02	-	160 6.30	17 0.67	M 8	6.4 0.25	57 2.24	6 0.24	190 7.48	11 0.43	6 0.24
26 1.02	-	192 7.56	17 0.67	M 8	6.4 0.25	57 2.24	6 0.24	227 8.94	11 0.43	6 0.24

**Specification**

**GN 565.4**

Aluminum

- Powder coated

Black, RAL 9005, textured finish

Red, RAL 3000, textured finish

Silver, RAL 9006, textured finish

- Anodized finish, natural color

- Plain, tumbled finish

- SW
- RS
- SR
- EL
- BL

**GN 565.9**

Stainless steel AISI 304

Matte shot-blasted finish

MT

• Load Rating Information → page 2068

• Stainless Steel Characteristics → page 2143

• RoHS compliant

**On request**

• Various metric size fasteners and kit packaging

**Information**

GN 565.4 and GN 565.9 arched pull handles are preferably used for such applications where easy sliding of folding doors or cabinet drawers can be operated with a single finger. Their shape blends well with modern design.

see also...

• Arched Pull Handles GN 665 (Aluminum, Ellipse Shaped Profile) → page 156

• Arched Pull Handles GN 424.1 / GN 424.5 (Steel / Stainless Steel, Ø 10 mm) → page 157

How to order (Aluminum)	1 Handle width b
1 2 3 4	2 Length l <sub>1</sub>
<b>GN 565.4-20-160-B-RS</b>	3 Type
	4 Finish

How to order (Stainless steel)	1 Handle width b
1 2 3 4	2 Length l <sub>1</sub>
<b>GN 565.9-20-192-A-MT</b>	3 Type
	4 Finish