



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread	$d_3$	$d_4$	$h$	$k$
40 1.57	M 8	12 .47	25 .98	10 .39	8.5 .33
40 1.57	M 10	13 .51	25 .98	10 .39	8.5 .33

**Specification**

- Plastic  
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to  
212 °F (100 °C)
- Black, matte finish



- Tapped insert  
Brass
- Plastic Characteristics → page QVX
- RoHS compliant

**On request**

- Additional thread sizes

**Information**

EN 567 lobed thumb nuts can be used to lock and secure by utilizing two thumb nuts on a threaded shaft. They also require minimal space due to their thin profile.

The ergonomic shape makes them easy to grip during use.

see also...

- Flat Knurled Nuts DIN 467 → page QVX

How to order <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>EN 567-40-M8-SW</b>	1	Handle diameter $d_1$
	2	Thread $d_2$
	3	Color

