



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	KU	KT					
18 0.71	M 6	M 6	10 0.39	15 0.59	40 1.57	12 0.47	2.5 0.10
21 0.83	M 6	M 6	10 0.39	17 0.67	50 1.97	13 0.51	2.5 0.10
23 0.91	M 8	M 8	13 0.51	19 0.75	65 2.56	14 0.55	2.5 0.10
26 1.02	M 10	M 10	13 0.51	21 0.83	80 3.15	16 0.63	2.5 0.10
28 1.10	M 10	M 10	13 0.51	22 0.87	90 3.54	16 0.63	2.5 0.10
31 1.22	M 12	-	14 0.55	25 0.98	102 4.02	20 0.79	2.5 0.10

**Specification**

- Plastic **KU**  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, shiny finish
- Plastic **KT**  
Technopolymer (Polypropylene PP)  
- Temperature resistant up to 176 °F (80 °C)  
- Black, matte finish
- Threaded spindle  
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

- GN 598.1 revolving handles are noted for their modern design, and they blend in well with the rectangular shaped rim handwheels.
- see also...**
- *Retractable Handles GN 598.5 (with Locking Mechanism)* → page 50
  - *Revolving Handles EN 598.2* → page 36

<b>How to order</b>	1	Material
	2	Handle diameter d <sub>1</sub>
	3	Thread d <sub>2</sub>
<b>GN598.1-KU-26-M10</b>		

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4