



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	<sup>3</sup> l <sub>1</sub>	d <sub>3</sub>	l <sub>2</sub>
13 0.51	M 6	9 0.35	8 0.31	18 0.71
14 0.55	M 6	9 0.35	8 0.31	20 0.79
16 0.63	M 6	9 0.35	8 0.31	23 0.91

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 176 °F (80 °C)  
- Black, matte finish
- Threaded spindle  
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Information**

GN 599.5 mini cylindrical revolving handles are mainly used on small handwheels (GN 736, GN 736.1) which are installed for control purposes where low torque is required (fingertip grip).

see also...

- *Knurled Control Knobs GN 736* → page 272
- *Knurled Control Knobs with Disposition for Scale GN 736.1* → page 273

<p>How to order</p> <p><b>GN599.5-14-M6-9</b></p>	<sup>1</sup> <sup>2</sup> <sup>3</sup>	<b>1</b> Handle diameter d <sub>1</sub>
		<b>2</b> Thread d <sub>2</sub>
		<b>3</b> Length l <sub>1</sub>