



**4** Type

**P** Press-on type

**Metric table**

<b>1</b> s <sub>1</sub>	<b>2</b> s <sub>2</sub>	<b>3</b> n	h ≈	Dimensions in: millimeters - inches
30 1.18	30 1.18	8 0.31	3 0.12	Grid size 30 1.18
30 1.18	60 2.36	8 0.31	3 0.12	30 1.18
40 1.57	40 1.57	10 0.39	4 0.16	40 1.57
40 1.57	80 3.15	10 0.39	4 0.16	40 1.57
45 1.77	45 1.77	10 0.39	4 0.16	45 1.77
45 1.77	60 2.36	10 0.39	4 0.16	45 1.77
45 1.77	90 3.54	10 0.39	4 0.16	45 1.77
80 3.15	80 3.15	10 0.39	4 0.16	40 1.57
90* 3.54	90 3.54	10 0.39	4 0.16	45 1.77

\* Only compatible with profile type L

**Specification**

- Plastic (Polyamide PA)  
Black
- *Plastic Characteristics* → page QVX
- RoHS



**Information**

Cover caps GN 60b make a visually appealing closure for the end faces of aluminum profiles, protecting against injuries from sharp cut edges and preventing the ingress of dust and dirt.

They can be fitted without machining the profile.

see also...

- *Aluminum Profiles GN 10b (Profile Type Light)* → page QVX
- *Aluminum Profiles GN 10b (Profile Type Heavy)* → page QVX

How to order	
<b>1</b> Width s <sub>1</sub>	
<b>2</b> Width s <sub>2</sub>	
<b>3</b> Slot width n	
<b>4</b> Type	
<b>5</b> Color	

**GN 60b-45 90 10-P-KS**