



**Metric table**



Dimensions in: millimeters - inches

| <b>h<sub>3</sub></b> | <b>d<sub>4</sub></b> | <b>d<sub>5</sub></b> |
|----------------------|----------------------|----------------------|
| 18<br><i>0.71</i>    | 22.5<br><i>0.89</i>  | 6.5<br><i>0.26</i>   |
| 19.5<br><i>0.77</i>  | 26.5<br><i>1.04</i>  | 8.5<br><i>0.33</i>   |
| 20.5<br><i>0.81</i>  | 29<br><i>1.14</i>    | 9<br><i>0.35</i>     |

**Specification**

- Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black-gray, similar to RAL 7021, matte finish
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

**Information**

EN 628.2 spacers are accessories for EN 628, EN 628.1, EN 628.3 and EN 628.4 bridge handles.

[see also...](#)

- [Product Family Ergostyle®](#) → page QVX
- [Bridge Handles EN 628](#) → page QVX
- [Bridge Handles EN 628.1](#) → page QVX
- [Flexible Bridge Handles EN 628.3](#) → page QVX
- [Bridge Handles EN 628.4](#) → page QVX

|                      |          |                       |
|----------------------|----------|-----------------------|
| How to order         | <b>1</b> | Height h <sub>3</sub> |
| <b>EN 628.2-20.5</b> |          |                       |