



- 2 Type**
- A Mounting with hex head screw
 - B Mounting with countersunk screw

Metric table



Dimensions in: millimeters - inches

l_1	$l_2 \pm 0.5$	l_3	b_1	b_2	d	h_1	h_2	h_3	h_4	t
114	93.5	74	35	19	6.5	33	7	11	9	5
4.49	3.68	2.91	1.38	0.75	0.26	1.30	0.28	0.43	0.35	0.20

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover (shiny finish):
 - DSG
 - DOR
 - DGR
 - DGB
 - DBL
 - DRT
 - DGN
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

Information

When using guards on machines and automation systems, which include double hinged doors, the EN 630 off-set “U” handles completely enclosed are a safety element for operator fingers while the doors are being used. Use of a colored safety cover makes identification easier.

Resistant to solvents, oils, grease and other chemical agents.

The cover is included but supplied unassembled.

see also...

- Product Family Ergostyle® → page 18
- Product Family Standard Parts for Profile Systems → page 18

How to order	
1	Length l_1
2	Type
3	Color of the cover

EN 630-114-B-DOR