



- 2 Type**
- A Mounting with hex head screw
 - B Mounting with countersunk screw

Metric table



Dimensions in: millimeters - inches

l_1	$l_2 \pm 0.5$	l_3	b_1	b_2	d	h_1	h_2	h_3	h_4	t
114	93.5	74	35	19	6.5	33	7	11	6	5
4.49	3.68	2.91	1.38	0.75	0.26	1.30	0.28	0.43	0.24	0.20

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black-gray, similar to RAL 7021, matte finish
- Color of the cover caps (shiny finish):
 - DSG Black-gray, RAL 7021
 - DOR Orange, RAL 2004
 - DGR Gray, RAL 7035
 - DGB Yellow, RAL 1021
 - DBL Blue, RAL 5024
 - DRT Red, RAL 3000
 - DGN Green, RAL 6017
- Strength Values → page 2081
- Plastic Characteristics → page 2135
- RoHS compliant

Information

- When using guards on machines and automation systems, which include double hinged doors, use of colored covers makes identification of the EN 630.1 off-set open U-handles easier.
- Resistant to solvents, oils, grease and other chemical agents.
- The covers are included but supplied unassembled.
- see also...
- Product Family Ergostyle® → page 18
 - Product Family Standard Parts for Profile Systems → page 18
 - Cabinet U-Handles GN 565.2
(Aluminum, Angled, Mounting from the Back or from the Operator's Side) → page 106
 - Cabinet U-Handles GN 425.1 (Offset) → page 144 / 145
 - T-Nut Assemblies GN 965 (for 30 / 40 mm T-Slot Profile Systems) → page 2048
 - T-Nut Assemblies GN 968 (for 30 / 40 / 45 mm T-Slot Profile Systems) → page 2058

<p>How to order</p> <p>EN 630.1-114-A-DOR</p>	1	Length l_1
	2	Type
	3	Color of the cover caps