



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l ≈ GN 6335.4						Length l ≈ GN 6335.5					d ₃	h ₁	h ₂
		16	20	25	30	35	45	20	25	30	40	55			
32 1.26	M 6	0.63	0.79	0.98	1.18	1.38	1.77	-	-	-	-	-	12 0.47	20 0.79	9 0.35
40 1.57	M 8	0.59	0.79	0.98	1.18	1.57	2.17	0.79	0.98	1.18	1.57	-	14 0.55	25 0.98	13 0.51
50 1.97	M 10	0.98	1.18	1.38	1.77	2.17	-	0.79	0.98	1.18	1.77	2.17	18 0.71	32 1.26	18 0.71
63 2.48	M 12	1.18	1.38	1.57	1.97	2.36	-	1.18	1.57	1.97	-	-	20 0.79	40 1.57	23 0.91
80 3.15	M 16	1.18	1.57	1.97	2.36	2.76	-	-	-	-	-	-	25 0.98	50 1.97	28 1.10

Specification

- **GN 6335.4**
 - Threaded stud
Steel, blackened finish
 - Hand knob
Cast iron, fettled and tumbled **SG**
- **GN 6335.5**
 - Threaded stud
Stainless steel AISI 303
 - Hand knob
Stainless steel precision casting AISI CF-8
Matte shot-blasted finish **ES**
 - Hand knob
Aluminum, forged
Matte, tumbled finish **AM**
Polished finish **AP**
- For all types the threaded stud is screwed in and secured by a cross-dowel pin.
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Special inch and metric stud lengths

Information

GN 6335.4 cast iron hand knobs extend the range of clamping applications and are perfect for medium to heavy duty clamping applications. GN 6335.5 hand knobs have very good corrosion resistant properties.

see also...

- *Hand Knobs GN 6335.4 (Plastic, with Steel Threaded Stud)* → page 634
- *Hand Knobs GN 6335.5 (Plastic, with Stainless Steel Threaded Stud)* → page 634
- *Star Knobs GN 5334 / GN 5334.4 (Stainless Steel)* → page 617
- *Wing Screws GN 433 (Stainless Steel)* → page 678
- *Wing Screws GN 835 (Stainless Steel)* → page 677

How to order (Steel threaded stud)	1 Material
GN 6335.4-SG-50-M10-35	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l

How to order (Stainless steel threaded stud)	1 Finish (Material)
GN 6335.5-AP-40-M8-20	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l