



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

² d ₁	³ d ₂	⁴ Length l					d ₃	h ₁	h ₂
40 1.57	M 8	20 0.79	25 0.98	30 1.18	40 1.57	-	14 0.55	25 0.98	13 0.51
50 1.97	M 10	20 0.79	25 0.98	30 1.18	45 1.77	55 2.17	18 0.71	32 1.26	18 0.71
63 2.48	M 12	30 1.18	40 1.57	50 1.97	-	-	20 0.79	40 1.57	23 0.91

Specification



- Hand knob
Stainless steel precision casting
AISI 316
Polished finish
- Threaded stud
Stainless steel A4
- The threaded stud is screwed in and secured by a cross-dowel pin (Stainless steel A4)
- Stainless Steel Characteristics → page QVX
- RoHS compliant

A4P

Information

GN 6335.5 hand knobs satisfy the dimensions of the DIN 6335 type L but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygienic requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- Hand Knobs GN 6335.4 / 6335.5 (Plastic) → page QVX
- Hand Knobs GN 6335.4 / 6335.5 (Cast Iron / Stainless Steel / Aluminum) → page QVX

How to order

¹ ² ³ ⁴
GN 6335.5-A4P-40-M8-25

- ¹ Material
- ² Handle diameter d₁
- ³ Thread d₂
- ⁴ Length l

