



Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂	3 l ₁		l ₂	d ₃	d ₄	b	h ₁	h ₂
48 1.89	M 6	20 0.79	30 1.18	1.5 0.06	13.5 0.53	4 0.16	7 0.28	24 0.94	5.5 0.22
55 2.17	M 8	20 0.79	30 1.18	1.8 0.07	16 0.63	5 0.20	8 0.31	28 1.10	6.5 0.26
70 2.76	M 10	20 0.79	30 1.18	2 0.08	20 0.79	6 0.24	10 0.39	36 1.42	8 0.31

Specification

4

- Wing body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, similar to RAL 7021, matte finish
- Threaded stud
Stainless steel AISI 303
- Tip
Plastic (Polyacetal POM)
- Color of the cover cap (matte finish):

●	DSG
●	DOR
●	DGR
●	DGB
●	DBL
●	DRT
●	DGN
- Stainless Steel Characteristics → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

Information

With the plastic tip on the stud, EN 633.10 wing screws are suitable for applications where marks and damage on the workpiece are unacceptable.

The slightly concave indentations on the ends of the wings help to position the fingers to apply the maximum force when tightening.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Product Family Ergostyle® → page QVX
- Star Knobs GN 6336.10 (with Brass / Plastic Tip) → page QVX
- Hollow Knurled Knobs GN 421.10 (with Brass / Plastic Tip) → page QVX

How to order	1
	Handle diameter d ₁
	Thread d ₂
	Length l ₁
	Color of the cover cap

1 2 3 4
EN 633.10-70-M10-30-DGB