



Metric table

Dimensions in: millimeters - inches

¹ b ₁	² l ₁ ±0.25	a	b ₂	d Thread	h -1	l ₂ ≈	l ₃	l ₄ ≈	l ₅ max.
26 1.02	350 13.78	17 0.67	14 0.55	M 8	69 2.72	526 20.71	328 12.91	18 0.71	9.5 0.37
26 1.02	450 17.72	17 0.67	14 0.55	M 8	69 2.72	632 24.88	428 16.85	18 0.71	9.5 0.37

Specification

- Handle
Aluminum
Powder coated
Black, RAL 9005, textured finish ● **SW**
Silver, RAL 9006, textured finish ● **SR**
- End pieces (for both SW and SR)
Zinc die-cast
Powder coated
Silver, RAL 9006, textured finish
- Set screws
Steel, zinc plated, blue passivated finish
Property class 5.8
- Hex nuts ISO 4032-M8
Steel, zinc plated
- Washers DIN 125
Steel, zinc plated
- *Load Rating Information* → page 2068
- *Strength Values of Screws* → page 2127
- **RoHS compliant**

Information

GN 665 arched pull handles are produced from elliptical extrusions, and are notable for their elegant design.

see also...

- *Arched Pull Handles GN 565.4 (Aluminum, Mounting from the Back or from the Operator's Side)* → page 155
- *Cabinet "U" Handles GN 428 (Aluminum)* → page 153

How to order

¹ ² ³
GN 665-26-450-SW

- ¹ Handle width b₁
- ² Length l₁
- ³ Finish