



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² l ₁ ±1							a	b	d ₂ Thread	h ₁	h ₂	l ₂	l ₃	t
30	300	350	400	500	600	700	1000	57	38	M 10	60	78	23	12	17
1.18	11.81	13.78	15.75	19.69	23.62	27.56	39.37	2.24	1.50		2.36	3.07	0.91	0.47	0.67

Specification

³

- Tube Ø 30x1.5 mm
Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Anodized finish, natural color ● **EL**
 - Stainless steel AISI 304
 - Ground, matte shiny finish ● **NG**
- Handle legs
Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 212 °F (100 °C)
 - Black, matte finish
- Tapped inserts
Brass
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

The handle tube of GN 667.2 tubular grip handles can be mounted without any further machining, allowing special lengths to be created easily.

On request

- Special lengths

How to order GN 667.2-30-1000-NG	¹	Handle diameter d ₁
	²	Length l ₁
	³	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4