



- 3 Type**
- A** Mounting from the back (tapped blind hole)
 - B** Mounting from the operator's side (only for $b_1 = 20$ mm)

Metric table

Dimensions in: millimeters - inches

| 1 b_1 | 2 l_1 | a | b_2 | d Thread | h_1 | h_2 | h_3 | l_2 | l_3 | l_4 | r | t_1 min. | t_2 |
|----------------|----------------|------------|------------|---------------|------------|-------------|-------------|--------------|-------------|-------------|------------|---------------|-----------|
| 20 0.79 | 130 5.12 | 10 0.39 | 23 0.91 | M 5 | 45 1.77 | 6.5 0.26 | 2.5 0.10 | 120 4.72 | 141 5.55 | 153 6.02 | 15 0.59 | 10 0.39 | 5 0.20 |
| 20 0.79 | 170 6.69 | 10 0.39 | 23 0.91 | M 5 | 45 1.77 | 6.5 0.26 | 2.5 0.10 | 160 6.30 | 181 7.13 | 193 7.60 | 15 0.59 | 10 0.39 | 5 0.20 |
| 20 0.79 | 190 7.48 | 10 0.39 | 23 0.91 | M 5 | 45 1.77 | 6.5 0.26 | 2.5 0.10 | 180 7.09 | 201 7.91 | 213 8.39 | 15 0.59 | 10 0.39 | 5 0.20 |
| 20 0.79 | 210 8.27 | 10 0.39 | 23 0.91 | M 5 | 45 1.77 | 6.5 0.26 | 2.5 0.10 | 200 7.87 | 221 8.70 | 233 9.17 | 15 0.59 | 10 0.39 | 5 0.20 |
| 30 1.18 | 262 10.31 | 12 0.47 | - | M 6 | 50 1.97 | - | - | 250 9.84 | - | - | 15 0.59 | 12 0.47 | - |
| 30 1.18 | 312 12.28 | 12 0.47 | - | M 6 | 50 1.97 | - | - | 300 11.81 | - | - | 15 0.59 | 12 0.47 | - |
| 30 1.18 | 362 14.25 | 12 0.47 | - | M 6 | 50 1.97 | - | - | 350 13.78 | - | - | 15 0.59 | 12 0.47 | - |
| 30 1.18 | 412 16.22 | 12 0.47 | - | M 6 | 50 1.97 | - | - | 400 15.75 | - | - | 15 0.59 | 12 0.47 | - |

Specification

- Handle
Aluminum
- Powder coated
Black, RAL 9005, textured finish
Silver, RAL 9006, textured finish
- Plain, tumbled finish
- Handle base
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish (for SW / BL)
- Light gray, matte finish (for SR)
- Socket cap screws DIN 7984
Steel
Zinc plated, blue passivated finish
- Load Rating Information → page 2068
- Plastic Characteristics → page 2135
- RoHS compliant

- **SW**
- **SR**
- **BL**

On request

- Special lengths
- Various metric size fasteners and kit packaging

Information

Cabinet U-handles GN 668 are manufactured from a bent aluminum profile. They can be mounted either from the back (type A) or by means of the handle base from the operator's side (type B).

see also...

- "Economical" Cabinet "U" Handles GN 728 (Aluminum, Mounting from the Back or from the Operator's Side) → page 120

| | |
|--------------|-----------------------------|
| How to order | 1 Handle width b_1 |
| | 2 Length l_1 |
| | 3 Type |
| | 4 Finish |

GN 668-20-170-B-SW