



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread		d <sub>3</sub>	h	t <sub>1</sub> min.	t <sub>2</sub> ±0.5
15 0.59	M 6	-	12 0.47	25 0.98	16 0.63	3.5 0.14
20 0.79	M 8	-	14 0.55	31 1.22	20 0.79	3.5 0.14
26 1.02	M 8	M 10	17 0.67	42 1.65	20 0.79	5 0.20
33 1.30	M 10	M 12	20 0.79	54 2.13	40 1.57	8 0.31
38 1.50	M 12	-	23 0.91	68 2.68	45 1.77	11 0.43
41 1.61	M 14	M 16	25 0.98	87 3.43	55 2.17	14 0.55

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, shiny finish
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

**Information**

EN 719 domed gear lever knobs are very often used in place of ball knobs DIN 319 on switch levers, gear levers etc. Knobs for such applications are often chosen for ergonomical reasons.

see also...

- *Domed Gear Lever Knobs EN 719.2 (Tapped or Press-On Type)* → page QVX

<p>How to order</p> <p><sup>1</sup> <sup>2</sup></p> <p><b>EN 719-20-M8</b></p>	1 Handle diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>