



Metric table

Dimensions in: millimeters - inches

Length l	a	b	d	h ₁	h ₂	t
86 ±0.5 3.39 ±0.02	14 0.55	23 0.91	5.4 0.21	44 1.73	15 0.59	5.5 0.22
117 ±0.5 4.61 ±0.02	16 0.63	25 0.98	6.4 0.25	49 1.93	15 0.59	6 0.24
132 ±1 5.20 ±0.04	16 0.63	26 1.02	6.4 0.25	53 2.09	15 0.59	8.5 0.33
179 ±1 7.05 ±0.04	16 0.63	27 1.06	6.4 0.25	57 2.24	15 0.59	6 0.24

Specification

- Handle
Plastic, Polypropylene (PP)
- Shock-resistant
- Operating temperature
-4 °F to +212 °F (-20 °C to +100 °C)
- Black, matte finish
- Tapped inserts
Brass, molded-in
- Strength Values → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Various metric and inch size fasteners and kit packaging

Information

EN 725.1 cabinet U-handles are well known for their smooth ergonomically shaped elliptical design. High impact strength. Resistant to solvents, oils, grease and other chemical agents.

see also...

- Cabinet "U" Handles GN 565.1 (Aluminum) → page QVX
- Cabinet "U" Handles GN 565.5 (Stainless Steel, Mounting from the Back or from the Operator's Side) → page QVX

How to order	1 Length l
EN 725.1-179	