



Metric table

Dimensions in: millimeters - inches

Length l	a	b	d	h ₁	h ₂	t
86 ±0.5 3.39 ±0.02	14 0.55	23 0.91	5.4 0.21	44 1.73	15 0.59	5.5 0.22
117 ±0.5 4.61 ±0.02	16 0.63	25 0.98	6.4 0.25	49 1.93	15 0.59	6 0.24
132 ±1 5.20 ±0.04	16 0.63	26 1.02	6.4 0.25	53 2.09	15 0.59	8.5 0.33
179 ±1 7.05 ±0.04	16 0.63	27 1.06	6.4 0.25	57 2.24	15 0.59	6 0.24

Specification

- Plastic
Technopolymer (Polypropylene PP)
- Shock-resistant
- Temperature resistant up to 212 °F (100 °C)
- Black, matte finish
- Tapped inserts
Brass, molded-in
- Strength Values → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Various metric and inch size fasteners and kit packaging

Information

EN 725.1 cabinet “U” handles are well known for their smooth ergonomically shaped elliptical design. High impact strength. Resistant to solvents, oils, grease and other chemical agents.

see also...

- Cabinet “U” Handles GN 565.1 (Aluminum) → page QVX
- Cabinet “U” Handles GN 565.5 (Stainless Steel, Mounting from the Back or from the Operator’s Side) → page QVX

How to order	1 Length l
EN 725.1-179	