



- 3 Type**
- A With arrow
  - B Neutral, without indicator point or scale
  - S With scale 0...9, 20 graduations
- 4 Identification no.**
- 1 With set screw
  - 2 With collet

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> H8 Bore		<b>2</b> d <sub>3</sub> Collet	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	d <sub>7</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	Length l	t
22 0.87	B 5	-	-	16 0.63	14 0.55	M 4	20 0.79	22 0.87	16 0.63	4.3 0.17	8 0.31	12.5 0.49	-
27 1.06	B 6	-	Z 6	20 0.79	18 0.71	M 4	25 0.98	26 1.02	20 0.79	4.3 0.17	9 0.35	14 0.55	14 0.55
34 1.34	B 6	B 8	Z 8	25 0.98	23 0.91	M 5	32 1.26	30 1.18	24 0.94	4.2 0.17	10 0.39	15 0.59	17 0.67
42 1.65	B 8	B 10	Z 10	32 1.26	30 1.18	M 5	40 1.57	34 1.34	28 1.10	4 0.16	11 0.43	16 0.63	20 0.79

**Specification**

- Body  
Aluminum  
Black, anodized finish
- Arrow (Type A) and scale (Type S)  
White, laser engraved
- Cover  
Plastic, light gray
- Collet / hex nut  
Brass
- Socket set screw DIN 916  
Stainless steel  
With internal hex and serrated point
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**On request**

- Special graduations, see  
„How to Order Graduations“ → page 328

**Information**

The light gray cover disk makes these GN 726.1 control knobs an aesthetically appealing choice. The cover is held in place by firmly pushing it into the recess. It can be removed by inserting a screw driver into the slot provided.

The collet type provides a simple way of positioning and locking the control knob to the shaft.

Other types than the standard scale can be supplied, see order examples on „How to Order Graduations“ → page 328.

see also...

- Control Knobs EN 626 (Technopolymer Plastic) → [www.jwwinco.com](http://www.jwwinco.com)
- Control Knob Flanges GN 826 (for Adjustable Spindles) → [www.jwwinco.com](http://www.jwwinco.com)

How to order	
<b>1</b>	Outside diameter d <sub>1</sub>
<b>2</b>	Bore d <sub>2</sub> (Collet d <sub>3</sub> )
<b>3</b>	Type
<b>4</b>	Identification no.

**GN 726.1-42-B10-A-1**