



2 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Metric table



Dimensions in: millimeters - inches

l_1	b	d_1 Thread	d_2	d_3	h_1	h_2	l_2	l_3	s	t_1 min.	t_2	
GN 728	GN 728.5											
120 4.72	120 4.72	22.5 0.89	M 6	6.4 0.25	11 0.43	42.5 1.67	6.5 0.26	147 5.79	108 4.25	8 0.31	10 0.39	6.5 0.26
180 7.09	-	27 1.06	M 8	8.4 0.33	13.5 0.53	47.5 1.87	7.5 0.30	214 8.43	165 6.50	10 0.39	12 0.47	8.5 0.33

Specification



- **GN 728**
Aluminum die-cast
- Powder coated
Black, RAL 9005, textured finish ● **SW**
Silver, RAL 9006, textured finish ● **SR**
- Plain, tumbled finish ○ **BL**
- **GN 728.5**
Stainless steel precision casting AISI CF-8
Matte shot-blasted finish
- [Load Rating Information](#) → page 2068
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

On request

- For certain minimum quantities, special colors
- Various metric size fasteners and kit packaging

Information

GN 728 and GN 728.5 "economical" cabinet "U" handles are a low-cost alternative in metal. The installation can be carried out from the back (type A) as well as from the operator's side (type B). Hole center dimension is identical in both versions, so they can be mounted in pairs opposite each other. Tumbled finish version not recommended to be anodized.

see also...

- [Product Family Standard Parts for Profile Systems](#) → page 18
- [Cabinet "U" Handles EN 528 \(Plastic, Mounting from the Operator's Side\)](#) → page 114
- [Cabinet "U" Handles EN 528.1 \(Plastic, Mounting from the Back\)](#) → page 116

How to order (Aluminum)	1	Length l_1
	2	Type
	3	Finish
GN 728-120-A-SW		

How to order (Stainless steel)	1	Length l_1
	2	Type
GN 728.5-120-B		