



2 Type

- A** Mounting from the operator's side (for identification no. 2 with four countersunk sealing screws)
- C** Mounting from the back

3 Identification no.

- 1** Without seal
- 2** With black seal
- 3** With blue seal (only Type C)

Metric table

Dimensions in: millimeters - inches

l₁	h₁	h₂	l₂	l₃	l₄	l₅	l₆ +1	l₇ +1	m₁	m₂
155	80	42	109	20	3.5	19.2	60	115	128	53
6.10	3.15	1.65	4.29	0.79	0.14	0.76	2.36	4.53	5.04	2.09

Specification

- Body
Stainless steel AISI 304
- Matte shot-blasted finish
- Electropolished finish
- Housing seal
Rubber, glued
- NBR, black (Identification no. 2)
- Silicone, blue (Identification no. 3)
FDA compliant
- Countersunk sealing screws DIN 7991 M5x16 (Type A, Identification no. 2)
Stainless steel A2
Polyamide coating on head
- Threaded studs (Type C)
Stainless steel AISI 304
Welded
- Protection class IP 66
- IP Protection Classes → page 2130
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 7332 gripping trays can be easily and quickly installed from the front using countersunk screws or from the back with threaded studs. Threaded studs are welded to the gripping tray.

Gripping trays with housing seal (identification no. 2 and 3) prevent the penetration of any dirt or liquids into the housing interior. The FDA compliant version also allows use in areas where food or pharmaceutical products are produced.

Type A is supplied with four additional countersunk sealing screws, which feature a polyamide coating on the head to create a tight seal.

see also...

- Gripping Trays EN 733 (Technopolymer Plastic, Screw-In Type) → page 200
- Gripping Trays EN 731 (Technopolymer Plastic, Clip-In Type) → page 198

How to order	
1 Length l₁	155
2 Type	A
3 Identification no.	1
4 Finish	GS

GN 7332-155-A-1-GS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4