



Metric table



Dimensions in: millimeters - inches

l ₁	b ₁	b ₂	b ₃	b ₄	h ₁	h ₂	l ₂	l ₃	s
130	59	31	41	48	29.5	3	100	124	1 ... 5
5.12	2.32	1.22	1.61	1.89	1.16	0.12	3.94	4.88	

Specification



- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 230 °F (110 °C)
- Color (matte finish):
Black-gray, RAL 7021 SG
White, RAL 9002 WS
- Self-tapping screws ISO 7049
Steel, zinc plated ST 3.5-20
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

Information

EN 739 gripping trays are designed for use on opening and closing sliding doors.
For mounting, the front body is first inserted into the opening of the housing and then the rear body is pushed up from behind to the housing wall. Finally, both parts are screwed together.
see also...
• *Product Family Ergostyle®* → page 18

How to order	
EN 739-130-SG	1 Length l ₁
	2 Color