



Metric table

1

l_1	b_1	b_2	b_3	b_4	h_1	h_2	l_2	l_3	s
130 5.12	59 2.32	31 1.22	41 1.61	48 1.89	29.5 1.16	3 0.12	100 3.94	124 4.88	1 ... 5

Specification

- 2
- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 230 °F (110 °C)
 - Color
 - Black-gray, RAL 7021, matte finish
 - White, RAL 9002, matte finish

● SG

○ WS
 - Self-tapping screws ISO 7049
Steel, zinc plated ST 3.5-20
 - Plastic Characteristics → page 2135
 - RoHS compliant

Information

EN 739 gripping trays are designed for use on opening and closing sliding doors.

For mounting, the front body is first inserted into the opening of the housing and then the rear body is pushed up from behind to the housing wall. Finally, both parts are screwed together.

see also...

- Product Family Ergostyle® → page 18

How to order	1	Length l_1
EN 739-130-SG	2	Color