



SS Stainless Steel

3 Type

- D** With tapped hole
- E** With threaded stud

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Type D	2 d ₃ Type E	d ₄	h	Length l	t min.
16 0.63	M 5	M 6	10 0.39	18 0.71	10 0.39	7 0.28
20 0.79	M 6	M 8	12 0.47	24 0.94	12 0.47	9 0.35
25 0.98	M 6	M 8	14 0.55	29 1.14	14 0.55	9 0.35
32 1.26	M 8	M 10	18 0.71	37 1.46	16 0.63	12 0.47
36 1.42	M 10	M 12	20 0.79	42 1.65	18 0.71	15 0.59

Specification

- **GN 75**
Steel
 - Fine turned
 - Blackened finish **—**
 - Zinc plated, blue passivated finish **ZB**
- **GN 75.5**
Stainless steel AISI 304
 - Matte shot-blasted finish **MT**
 - Highly polished finish **PL**
- *Stainless Steel Characteristics* → page 2143
- *RoHS compliant*

Information

Mushroom shaped knobs GN 75 / GN 75.5 boast a compact and timeless design. Their non-scooping geometry combats dirt build-up and makes cleaning easier.

Mushroom shaped knobs GN 75 made of steel are mainly used in mechanical engineering. Mushroom shaped knobs GN 75.5 can be used in aggressive environments thanks to the stainless steel used.

see also...

- *Push / Pull Knobs GN 676.1 (Steel, Blackened Finish)* → page 77
- *Push / Pull Knobs GN 676.2 (Steel, Zinc Plated)* → page XYZ
- *Push / Pull Knobs GN 676.5 (Stainless Steel)* → page 77

On request

- Stainless steel A4 quality

How to order (Steel, blackened finish)	1 Handle diameter d ₁
GN 75-25-M6-D	2 Threaded stud d ₃ (Thread d ₂)
	3 Type
How to order (Steel, zinc plated)	1 Handle diameter d ₁
GN 75-25-M8-E-ZB	2 Threaded stud d ₃ (Thread d ₂)
	3 Type
	4 Finish
How to order (Stainless steel)	1 Handle diameter d ₁
GN 75.5-25-M8-E-MT	2 Threaded stud d ₃ (Thread d ₂)
	3 Type
	4 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4