



3 Type
D With tapped hole
E With threaded stud

Metric table

Dimensions in: millimeters - inches							
1 d ₁	2 d ₂ Type D	3 d ₃ Type E	d ₄	d ₅	h	Length l	t min.
20 0.79	M 5	M 5	14 0.55	14.8 0.58	24 0.94	10 0.39	7 0.28
25 0.98	M 6	M 6	16 0.63	16.8 0.66	29 1.14	12 0.47	9 0.35
32 1.26	M 8	M 8	18 0.71	18.8 0.74	37 1.46	14 0.55	12 0.47

Specification

- Stainless steel AISI 316L
 - Matte finish (Ra < 0.8 µm) **MT**
 - Polished finish (Ra < 0.8 µm) **PL**
- Sealing ring
 - H-NBR **H**
Temperature resistant from -13 °F to +302 °F (-25 °C to +150 °C)
 - EPDM **E**
Temperature resistant from -40 °F to +248 °F (-40 °C to +120 °C)
 - Blue
 - Hardness 85±5 shore A
 - FDA compliant
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Accessory

- Sealing rings GN 7600 → page 1683

Information

GN 75.6 mushroom shaped knobs are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

GN 75.6 mushroom shaped knobs have a compact and timeless design.

see also...

- Product Family [Hygienic Design](#) → page 16

How to order	
1	Handle diameter d ₁
2	Tapped hole d ₂ (Threaded stud d ₃)
3	Type
4	Finish
5	Sealing ring material

GN 75.6-25-M6-E-MT-H