



Metric table

1

2

d ₁	d ₂ Thread	d ₃	h	t ₁ min.	t ₂ ±0.5
35 1.38	M 8	19 0.75	27 1.06	15 0.59	3.5 0.14
45 1.77	M 10	24 0.94	34 1.34	20 0.79	4 0.16

Dimensions in: millimeters - inches

Specification

- Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, shiny finish
 - Molded-in thread
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- With threaded stud

Information

EN 77 mushroom shaped knobs are great for use on push-pull type applications. The smooth shape gives the operator a comfortable grip.

How to order	1	Handle diameter d ₁
EN 77-35-M8	2	Thread d ₂