



SS Stainless Steel

Metric table

		Dimensions in: millimeters - inches		
1 d ₁ Bore	2 d ₂ Bore		For tube outside Ø	Standard description in inch
B 42.4	B 42.4	-	42.4 16.69	1 ¼"
B 48.3	B 42.4	B 48.3	48.3 19.02	1 ½"
B 60.3	B 42.4	B 48.3	60.3 23.74	2"

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Black, matte finish
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 934
Stainless steel AISI 304
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- RoHS compliant

Information

- see also...
- *T-Angle Connector Clamps GN 192 (Aluminum)* → page XYZ
 - *Construction Tubes GN 990* → page XYZ

How to order EN81-B48.3-B42.4	1 Bore d ₁
	2 Bore d ₂

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

