



**Metric table**

Dimensions in: millimeters - inches

| Size | b <sub>1</sub> | b <sub>2</sub> | b <sub>3</sub> | d <sub>1</sub> | d <sub>2</sub> | h           | t           |
|------|----------------|----------------|----------------|----------------|----------------|-------------|-------------|
| 220  | 22<br>0.87     | 13<br>0.51     | 5<br>0.20      | -              | -              | 60<br>2.36  | 55<br>2.17  |
| 440  | 31<br>1.22     | 20<br>0.79     | 8<br>0.31      | -              | -              | 86<br>3.39  | 77<br>3.03  |
| 850  | -              | -              | -              | 30<br>1.18     | 22<br>0.87     | 119<br>4.69 | 112<br>4.41 |
| 1540 | -              | -              | -              | 34<br>1.34     | 25<br>0.98     | 119<br>4.69 | 112<br>4.41 |

**Specification**

- Plastic
- RoHS compliant

**Information**

Handles GN 810.15 are accessory for knee lever modules GN 810.12 / GN 810.13.

see also...

- Knee Lever Modules GN 810.12 (with Horizontal or Vertical Mounting Base) → page QVX
- Knee Lever Modules GN 810.13 (with Weldable Base) → page QVX
- Arm Levers GN 810.16 → page QVX
- Clamping Arm Extenders GN 810.17 → page QVX
- Bushings GN 810.18 → page QVX
- Base Plates GN 810.19 → page QVX

|                      |   |      |
|----------------------|---|------|
| How to order         | 1 | Size |
| <b>GN 810.15-220</b> |   |      |