



Metric table

Dimensions in: millimeters - inches

d Bore	For tube outside Ø	Standard description in inch
B 42.4	42.4 1.67	1 ¼"
B 48.3	48.3 1.90	1 ½"
B 60.3	60.3 2.37	2"

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Black, matte finish
- Hex screws DIN 931
Stainless steel AISI 304
- Hex nuts DIN 934
Stainless steel AISI 304
- Washers
Stainless steel AISI 304
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Information

- see also...
- *Tripod Support Bases EN 82 (Plastic)* → page QVX
 - *Leveling Feet* → starting from page XYZ
 - *Construction Tubes GN 990* → page XYZ

How to order	1 Bore d
EN83-B48.3	

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

