



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

| <sup>1</sup><br>d <sub>1</sub><br>Bore | <sup>2</sup><br>d <sub>2</sub><br>Bore |        | For tube outside Ø | Standard description in inch |
|--|--|--------|--------------------|------------------------------|
| B 42.4                                 | B 42.4                                 | -      | 42.4<br>1.67       | 1 ¼"                         |
| B 48.3                                 | B 42.4                                 | B 48.3 | 48.3<br>1.90       | 1 ½"                         |
| B 60.3                                 | B 42.4                                 | B 48.3 | 60.3<br>2.37       | 2"                           |

**Specification**

- Body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 212 °F (100 °C)  
- Black, matte finish
- Hex screws DIN 931  
Stainless steel AISI 304
- Hex nuts DIN 934  
Stainless steel AISI 304
- Washers  
Stainless steel AISI 304
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- RoHS compliant

**Information**

- see also...
- *Bipod Support Bases EN 85 (Plastic)* → page QVX
  - *Leveling Feet* → starting from page XYZ
  - *Construction Tubes GN 990* → page XYZ

|   |                       |
|---|-----------------------|
| <p>How to order</p> <p><sup>1</sup> <sup>2</sup></p> <p><b>EN84-B60.3-B42.4</b></p> | 1 Bore d <sub>1</sub> |
|   | 2 Bore d <sub>2</sub> |