



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub> Bore	<b>2</b> d <sub>2</sub> Bore		For tube outside Ø	Standard description in inch
B 42.4	B 42.4	-	42.4 1.67	1 ¼"
B 48.3	B 42.4	B 48.3	48.3 1.90	1 ½"
B 60.3	B 42.4	B 48.3	60.3 2.37	2"

**Specification**

- Body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 212 °F (100 °C)  
- Black, matte finish
- Hex screws DIN 931  
Stainless steel AISI 304
- Hex nuts DIN 934  
Stainless steel AISI 304
- Washers  
Stainless steel AISI 304
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- RoHS compliant

**Information**

- see also...
- *Bipod Support Bases EN 84 (Plastic)* → page QVX
  - *Leveling Feet* → starting from page XYZ
  - *Construction Tubes GN 990* → page XYZ

<p>How to order</p> <p><b>EN85-B42.4-B42.4</b></p>	<b>1</b> Bore d <sub>1</sub>
	<b>2</b> Bore d <sub>2</sub>

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

