



**Metric table**

Dimensions in: millimeters - inches

<b>d<sub>1</sub> h6</b>	<b>d<sub>2</sub></b>	<b>Length l</b>
7 0.28	5.1 0.20	4 0.16
9 0.35	6.1 0.24	4 0.16
11 0.43	8.1 0.32	4 0.16
13 0.51	10.1 0.40	4 0.16

**Specification**

- Steel, blackened finish
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

GN 870 centering guide bushings ensure accurate location of the jaw blocks and brackets, as well as the pneumatic fastening clamps.  
At the same time, they absorb side thrust and eliminate excessive load on the mounting screws.

How to order <b>GN870-11</b>	1 Diameter d <sub>1</sub>
---------------------------------	---------------------------

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

