



SS Stainless Steel

Metric table

1 2 3

Dimensions in: millimeters - inches

d ₁	b	l ₁	d ₂	l ₃	Size	GN 852 / GN 852.3		Size	GN 852.1	
						r at w ₂ =0	w ₂		r at w ₂ =0	w ₂
M 10	46 1.81	129* 5.08	9 0.35	45 1.77	1700	96 3.78	15 0.59	1400	95 3.74	15 0.59
M 10	46 1.81	149** 5.87	9 0.35	52 2.05	1700	106 4.17	22 0.87	1400	109 4.29	22 0.87
M 10	46 1.81	179 7.05	9 0.35	45 1.77	1700	146 5.75	15 0.59	1400	145 5.71	15 0.59
M 10	46 1.81	209 8.23	9 0.35	45 1.77	1700	176 6.93	15 0.59	1400	175 6.89	15 0.59
M 10	46 1.81	259 10.20	9 0.35	45 1.77	1700	226 8.90	15 0.59	1400	225 8.86	15 0.59
M 12	55 2.17	151* 5.94	10.8 0.43	70 2.76	4000	107 4.21	25 0.98	-	-	-
M 12	55 2.17	211 8.31	10.8 0.43	70 2.76	4000	156 6.14	36 1.42	-	-	-
M 12	55 2.17	361 14.21	10.8 0.43	70 2.76	4000	306 12.05	36 1.42	-	-	-
M 12	55 2.17	421 16.57	10.8 0.43	70 2.76	4000	366 14.41	36 1.42	-	-	-

* These U-bolt latch lengths are included in the delivery of standard orders for GN 852 / GN 852.3.
** This U-bolt latch length is included in the delivery of standard orders for GN 852.1 and is only available in steel.

Specification

4

- Body
Steel
Zinc plated, blue passivated finish **ST**
- Body
Stainless steel AISI 304 **NI**
- Hex nuts (with Polyamide insert)
DIN 936 / DIN 985
- Steel, zinc plated (for ST)
- Stainless steel (for NI)
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

GN 951.2 square U-bolts are offered in a variety of length options for use with GN 852, GN 852.1 and GN 852.3 latch type toggle clamps.

see also...

- *Heavy Duty Latch Type Toggle Clamps GN 852* → page 812 / 814
- *Heavy Duty Latch Type Toggle Clamps GN 852.1* → page 820
- *Heavy Duty Latch Type Toggle Clamps GN 852.3* → page 816 / 818

How to order

1 2 3 4
GN951.2-M10-46-259-ST

- 1 Thread d₁
- 2 Width b
- 3 Length l₁
- 4 Material