



Metric table

Dimensions in: millimeters - inches

1 b		2 l₁	3 l₂	l₃	l₄
Nominal dimension	Actual dimension				
30 1.18	28 1.10	30 1.18	30 1.18	3 0.12	6.8 0.27
40 1.57	38 1.50	40 1.57	40 1.57	4 0.16	7.2 0.28
45 1.77	43 1.69	45 1.77	45 1.77	4 0.16	11.5 0.45

Specification

- Plastic
Technopolymer (Polyamide PA)
Black, RAL 9005, textured finish
- *Plastic Characteristics* → page QVX
- **RoHS compliant**



Information

GN 963 cover caps are suitable for use with GN 960 and GN 961 angle brackets for profile systems. After the angle brackets are assembled, the cover caps are snapped into place via four lugs. They give the angle brackets an attractive appearance and protect against dirt.

Even after repeated use, the cover caps will remain firmly in place attached to the angle brackets, thanks to the elastic snap-type lugs.

see also...

- *Angle Brackets for 30/40 mm Profile Systems GN 961* → page QVX
- *Angle Brackets for 30/40/45 mm Profile Systems GN 960* → page QVX

How to order

GN 963-40-40-40-SW

- 1** Width b
- 2** Length l₁
- 3** Length l₂
- 4** Finish