



- 5 Type**
- A Without bores
 - B With bores

Metric table

Dimensions in: millimeters - inches

2 h_1		3 b_1	4 l_1	b_2	d	h_2	l_2	m	s
ALM	STB								
30 1.18	30 1.18	30 1.18	30 1.18	18 0.71	6.2 0.24	18 0.71	15 0.59	-	4 0.16
30 1.18	30 1.18	30 1.18	60 2.36	18 0.71	6.2 0.24	18 0.71	15 0.59	30 1.18	4 0.16
40 1.57	40 1.57	40 1.57	40 1.57	24 0.94	8.2 0.32	24 0.94	20 0.79	-	5 0.20
40 1.57	40 1.57	40 1.57	80 3.15	24 0.94	8.2 0.32	24 0.94	20 0.79	40 1.57	5 0.20
50 1.97	-	50 1.97	50 1.97	30 1.18	10.2 0.40	30 1.18	25 0.98	-	6 0.24
50 1.97	-	50 1.97	100 3.94	30 1.18	10.2 0.40	30 1.18	25 0.98	50 1.97	6 0.24

Specification

- Structural steel
Drawn, with sharp edges
Blackened finish
- Aluminum
Pressed
Matte, tumbled finish
- RoHS compliant



STB

ALM

Information

GN 970 connecting brackets are used universally for right-angle connecting and mounting of e.g. base plates or covers.

Type A allows for the use of hole patterns specific to the application as well as mounting by welding.

Type B connecting brackets have 2 or 4 bores depending on the length l_1 .

see also...

- *Connecting Brackets GN 967* → www.jwwinco.com

<p>How to order</p> <p style="font-size: 2em; font-weight: bold;">GN970-STB-40-40-80-A</p>	1 Material
	2 Height h_1
	3 Width b_1
	4 Length l_1
	5 Type