



SS Stainless Steel

3 Type

- A Without handle
- F With fixed handle

Inch table

1 d_1	2 d_2 Bore		d_3	b	l_1	l_2	l_3
1.00* 25.4	B 1/4	Blank	0.50 12.7	0.38 9.7	0.63 16.0	0.81 20.6	-
2.00 50.8	B 3/8	Blank	0.81 20.6	0.56 14.2	0.88 22.4	1.13 28.7	1.28 32.5
3.00 76.2	B 5/8	Blank	1.25 31.8	0.69 17.5	0.88 22.4	1.25 31.8	1.94 49.3

Dimensions in: inches - millimeters

* Only available in type A

Specification

- **ALCK**
Machined from aluminum bar stock
- Anodized finish, natural color
- Polished to a high luster
- **SSCK**
Stainless steel AISI 303
- Outer rim knurled
- Keyways *WN / DIN 6885* → page *XYZ / XYZ*
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes and other handle types etc.

Information

ALCK /SSCK control knobs are used in applications that require more hand control such as gauging fixtures, precision instruments, printing equipment or where a high quality knob is necessary.
No mounting hole in knob without handle.

How to order (Aluminum)	1 Knob diameter d_1
ALCK-3.00-B5/8-F	2 Bore diameter d_2
	3 Type
How to order (Stainless steel)	1 Knob diameter d_1
SSCK-2.00-BLANK-A	2 Bore diameter d_2
	3 Type