



Inch table

Dimensions in: inches - millimeters

² d ₁	³ d ₂ Thread									t ₁
0.75 19.1	10 x 32	10 x 24	-	-	-	-	-	-	-	0.38 9.7
1.00 25.4	10 x 32	10 x 24	-	-	-	-	-	-	-	0.38 9.7
1.00 25.4	1/4 x 20	1/4 x 28	5/16 x 18	5/16 x 24	3/8 x 16	-	-	-	-	0.50 12.7
1.38 35.1	1/4 x 20	1/4 x 28	5/16 x 18	3/8 x 16	3/8 x 24	5/16 x 24	7/16 x 20	1/2 x 13	1/2 x 20	0.63 16.0
1.88 47.8	3/8 x 16	3/8 x 24	5/8 x 11	1/2 x 13	1/2 x 20	5/8 x 18	-	-	-	0.75 19.1

Specification

- Steel, highly polished **ST**
- Brass **MS**
 - Highly polished
 - Corrosion resistant in water
- Tapped hole for mounting
- RoHS compliant (only material ST)

Information

BK ball knobs are highly polished and turned from a solid bar stock. They are used on fixtures, machine tools, jigs and assemblies.

see also...

- *Ball Knobs DIN 319 (Metric, Steel, Stainless Steel and Aluminum)* → page 54

How to order	¹ Material
² BK-MS-1.00-5/16X18	² Handle diameter d ₁
³	³ Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4