



Inch table

¹ d ₁	² d ₂		³ Length l ±0.06	d ₃	h ₁	h ₂ min.	t
1.38 35.1	1/4 x 20	-	0.50 12.7	0.69 17.5	0.86 21.8	0.41 10.4	-
1.38 35.1	1/4 x 20	5/16 x 18	1.00 25.4	0.69 17.5	0.86 21.8	0.41 10.4	0.50 12.7
1.75 44.5	5/16 x 18	3/8 x 16	0.75 19.1	1.06 26.9	1.22 31.0	0.66 16.8	0.50 12.7
2.38 60.5	5/16 x 18	-	-	0.75 19.1	1.34 34.0	0.63 16.0	0.50 12.7
2.38 60.5	3/8 x 16	-	-	0.75 19.1	1.34 34.0	0.56 14.2	0.50 12.7
2.38 60.5	1/2 x 13*	-	-	1.25 31.8	1.34 34.0	0.56 14.2	0.56 14.2

Dimensions in: inches - millimeters

*This size has a zinc plated steel tapped insert

Specification

- Fluted star knob
Polypropylene plastic
- Temperature resistant up to 150 °F (66 °C)
- Black, textured finish
- Tapped Insert
- Brass
- Steel, zinc plated (thread d₂=1/2x13)
- Threaded stud
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- Additional thread sizes

Information

FKBH and FKZS fluted star knobs are an economical choice for light duty clamping or securing applications.

see also...

- *Fluted Star Knobs FKTH (with Tapped Through Insert)* → page 589

How to order (With brass tapped insert) ¹ ² FKBH-1.75-5/16X18	1	Handle diameter d ₁
	2	Thread d ₂
How to order (With steel threaded stud) ¹ ² ³ FKZS-1.38-1/4X20-0.50	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l