



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂		d ₃	h ₁	h ₂	t
1.38 35.1	1/4 x 20	-	0.69 17.5	0.84 21.3	0.41 10.4	0.50 12.7
1.75 44.5	1/4 x 20	-	1.06 26.9	1.22 31.0	0.66 16.8	0.50 12.7
1.75 44.5	5/16 x 18	-	1.06 26.9	1.22 31.0	0.66 16.8	0.50 12.7
1.75 44.5	3/8 x 16	-	1.06 26.9	1.22 31.0	0.63 16.0	0.50 12.7
2.38 60.5	5/16 x 18	3/8 x 16	1.25 31.8	1.31 33.3	0.63 16.0	0.50 12.7

Specification

- Fluted star knob
Polypropylene plastic
- Temperature resistant up to 150 °F (66 °C)
- Black, textured finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- Additional thread sizes

Information

FKTH fluted star knobs are an economical choice for light duty clamping or securing applications.
 see also...
 • *Fluted Star Knobs FKBH (with Blind Tapped Insert)* → page 588

How to order ¹ ² FKTH-1.75-3/8X16	1	Handle diameter d ₁
	2	Thread d ₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4