



**3 Type**

- A** Without locking element
- N** With locking element

**Inch table**

1		2		Dimensions in: inches - millimeters			
d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>			
2.25 57.2	1/4 x 20	5/16 x 18	3/8 x 16	3/8 x 24*	0.84 21.3	0.78 19.8	0.28 7.1

\*This size is only available in Type A

**Specification**

- Five-lobed knob  
Polypropylene plastic
  - Temperature resistant up to 275 °F (135 °C)
  - Black, matte finish
- Tapped insert / hex nut  
Steel, zinc plated
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**On request**

- Additional thread sizes

**Information**

FSK five-lobed knobs are perfect for light duty clamping on office chairs for example, but can be used for a variety of other applications.

How to order	1 Handle diameter d <sub>1</sub>
<b>FSK-2.25-1/4X20-A</b>	2 Thread d <sub>2</sub>
	3 Type